

5µm Aperture Diameter, Mounted, Precision Pinhole



5µm Aperture Diameter, Mounted, Precision Pinhole, #56-274

Stock **#56-274** 3-5 DAYS

⊖ 1 ⊕

A\$140.80

ADD TO CART

Qty 1-5

A\$140.80

Qty 6+

A\$124.64

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:

Mounted

Outer Diameter (mm):

25 +0.4/-0.000

Construction:

Stainless Steel

Fixed Aperture Diameter (µm):

Thickness (mm):
0.01 Nominal

Aperture Tolerance (µm):
±1

Mount Thickness (mm):
1.25 ±0.05

Aperture Centration (µm):
±125

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
