

5mW, 635nm Alignment Laser Diode



Red and IR Alignment Laser Diode

Stock #37-030 3-5 DAYS

-

1

+

A\$214.40

ADD TO CART

Qty 1-9

A\$214.40

Qty 10+

A\$188.64

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
-10 to 50

Operating Voltage (V):
5

Output Power (mW):

5
Wavelength (nm): 635.00
Wavelength Tolerance (nm): ±5
Power Supply: Power Supply Required and Sold Separately. USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Beam Diameter (mm): 3 x 1 Typical
Beam Divergence (mrad): Major Axis: 0.6 Minor Axis: 0.2
Laser Class - CDRH: IIIb
Color: Red
Length (mm): 36.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
