

5mW, 808nm Alignment Laser Diode



Red and IR Alignment Laser Diode

Stock **#19-450** [CONTACT US](#)

-

1

+

A\$214.40

ADD TO CART

Qty 1-9

A\$214.40

Qty 10+

A\$184.32

Volume Pricing

[Request Quote](#)

Get Product Downloads



Operating Temperature (°C):
-10 to 50

Operating Voltage (V):
5

Output Power (mW):
5

Wavelength (nm):

808.00
Wavelength Tolerance (nm): ±5
Power Supply: Power Supply Required and Sold Separately. USA: #83-855 Europe: #83-855 Japan: #13-640 Korea: #33-770 China: #83-855
Modulation Frequency (kHz): 0 - 10
Beam Diameter (mm): 2 x4 typical
Beam Divergence (mrad): <5.0
Laser Class - CDRH: IIIb
Color: infrared
Length (mm): 36.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
