

[All Products](#) / [Imaging Lenses](#) / [Zoom Lenses](#) / [4K Wide Angle Lenses](#)

[See all 21 Products in Family](#)

6 - 10mm FL, C-Mount, Manual Iris, Varifocal 4K Lens



Image represents #22-825: Design will vary by stock number.

Stock #22-825 3-5 DAYS

⊖ 1 ⊕

A\$1,888.00

ADD TO CART

Qty 1+
A\$1,888.00
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
Manual Iris

Length (mm):
46.50

Maximum Diameter (mm):
59

Weight (g):
70

Horizontal Field of View @ Max Sensor Format: 112 - 44
Type: Varifocal Lens
Maximum Sensor Format: 1/1.7"
Working Distance (mm): 500 - ∞
Mount: C-Mount
Aperture (f/#): F/1.7 to closed
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

