

[See all 21 Products in Family](#)

6 - 10mm FL, C-Mount, Manual Iris, Varifocal 4K Lens



Image represents #22-825; Design will vary by stock number.

Stock **#22-825** **1 In Stock**

⊖ 1 ⊕ A\$2,016⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,016.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Varifocal Lens **Type:**

Physical & Mechanical Properties

Variable Iris **Iris Option:**

46.50 **Length (mm):**

59 **Maximum Diameter (mm):**

70 **Weight (g):**

Optical Properties

Horizontal Field of View @ Max Sensor Format:
112 - 44

6-10 **Focal Length Range (mm):**

500 - ∞ **Working Distance (mm):**

F/1.7 to closed **Aperture (f/#):**

VIS **Lens Wavelength Range:**

Sensor

1/1.7" **Maximum Sensor Format:**

Threading & Mounting

C-Mount **Mount:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true Day/Night cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.