

[See all 7 Products in Family](#)

6 Watt, 230V, 365nm UV Curing Lamp



6 Watt, 230V, 365nm UV Curing Lamp, #86-805

Stock **#86-805** [CONTACT US](#)

-

1

+

A\$560⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$560.00 each
Need More?	Request Quote

Product Downloads

General	
Voltage converter required for use in U.S.	Note:
Optical Properties	
365.00	Wavelength (nm):
2300	Irradiance at 76.2mm (μW/cm²):
Hardware & Interface Connectivity	

6W, 230V	Power Requirement:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

Stands are not included, but recommended for hands free curing or analysis.

- 4-Watt and 6-Watt Models Centered at 365nm
- Stands are Available for Hands Free Curing
- Portable, High Intensity Design

Handheld UV Curing Lamps are portable benchtop lamps designed for a variety of applications including the fluorescence of stained gels, sterilization, or UV curing. These lamps feature ergonomically designed handles with conveniently placed on/off switches. These lamps are portable, with a high-intensity design. Handheld UV Curing Lamps are ideal for quickly curing Edmund Optics' full line of [Norland Optical Adhesives](#). These lamps are available in 4-watt and 6-watt models centered at 365nm.

Note: Stands are not included, but are recommended for hands free curing or analysis.