

600 Grooves, 12.7mm Sq, 28.7° Groove Angle Grating



Stock #49-576 3-5 DAYS

- 1 + **A\$160.00**

ADD TO CART

Qty 1-9
A\$160.00
Qty 10+
A\$144.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
600

Wavelength Range (nm):
400 - 700

Blaze Angle (°):
28.7

Dimensions (mm): 12.70 x 12.70
Construction: Blazed (Ruled) Grating
Length (mm): 12.70
Substrate: ☐ B270
Thickness (mm): 3.00 ±0.5
Type: Transmission Diffraction Grating
Wavelength: VIS
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5
Groove Angle (°): 28.7

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
