

## 600 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock #38-566 **3 In Stock**

⊖ 1 ⊕ A\$1,216<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	A\$1,216.00 each
Qty 5+	A\$1,156.48 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

Length (inches):  
3.00

Pattern Size (mm):  
12.7 x 25.4

Thickness (mm):  
1.10

Width (inches):  
1.00

### Optical Properties

---

Vacuum Deposited Chrome	<b>Coating:</b>
600.00	<b>Frequency (lp/mm):</b>
Float Glass	<b>Substrate:</b> <input type="checkbox"/>
3.00	<b>Optical Density OD (Average):</b>

---

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 240:</b>

---

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
  - Ideal for Reticle and Field Calibration Requirements
  - Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).
- Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.