

TECHSPEC® 6.0mm Diameter, Fused Silica Ball Lens



Stock **#67-387** 3-5 DAYS

- 1 + **A\$101.60**

ADD TO CART

Qty 1-10
A\$101.60
Qty 11+
A\$80.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:

Ball Lens
Wavelength Range (nm): 200 - 2200
Index of Refraction n_d: 1.458
Sphericity (μm): 0.625
Diameter Tolerance (μm): ± 5.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant