

60X Objective, Nikon CFI Plan Fluor

See More by [Nikon](#)



Nikon CFI Plan Fluor Objectives

Stock **#88-382** 3-5 DAYS

- 1 +

A\$5,395.20

ADD TO CART

Qty 1+
A\$5,395.20

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.11 - 0.23

Field of View (mm):
0.42

Horizontal Field of View, 1/2" Sensor:
0.11mm

Horizontal Field of View, 2/3" Sensor:
0.15mm

Model Number:

MRH00602
Length excluding Threads (mm): 59.50
Magnification: 60X
Maximum Diameter (mm): 31.5
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.85
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Working Distance (mm): 0.3
Weight (g): 154.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 25.2
Parfocal Length (mm): 59.5
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View