

TECHSPEC® 6.25mm Dia x -50mm FL NIR I Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #69-813 3-5 DAYS



1



A\$127.20

ADD TO CART

Qty 1-5

A\$127.20

Qty 6+

A\$101.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.2

Effective Focal Length EFL (mm):
-50.00

Substrate: ☐
[N-BK7](#)

f/#: 8.00
Numerical Aperture NA: 0.06
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): -51.32
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Edge Thickness ET (mm): 2.19
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -25.84
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant