

6.25mm Diameter Unmounted, Linear Glass Polarizing Filter



Stock **#43-782** [CONTACT US](#)

⊖ 1 ⊕

A\$65.60

ADD TO CART

Qty 1-5
A\$65.60
Qty 6+
A\$51.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25

Extinction Ratio:
100:1

Substrate: ☐
Polymer Film on [B270](#)

Operating Temperature (°C):

-15 to +70
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): Single: ~30
Type: Linear Polarizer
Parallelism (arcmin): <3
Dimensional Tolerance (mm): +0.0/-0.2
Bevel: Protective bevel as needed
Construction: Dichroic Polarizing Film on Glass
Edges: Cut
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): 4 - 6λ
Polarization Efficiency (%): 95

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View