

625nm, 6" High Brightness LED Line Light

See More by [Advanced Illumination](#)



Stock **#66-846** [CONTACT US](#)

-

1

+

A\$921.60

ADD TO CART

Qty 1+

A\$921.60

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Operating Lifetime (hours):
50,000

Mount:
T-Slot for M6 Nut

Operating Voltage (V):
24 DC

Dimensions (mm): 171.3 L x 33.8 W x 27.9 D
Wavelength (nm): 625.00
Weight (g): 300.00
Working Distance (inches): 12.00
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m): 2
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Line Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)