

625nm, Strobed, LED Linear Axial Diffuse Light

See More by [Advanced Illumination](#)



Stock **#83-311** [CONTACT US](#)

⊖ 1 ⊕ **A\$5,467.20**

ADD TO CART

Qty 1+
A\$5,467.20

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: Red
Model Number: DL110-625-I3
Operating Temperature (°C): 0 to 60
Wavelength (nm): 625.00

Weight (lbs): 1.3
Working Distance (mm): 12.7 - 50
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10
Number of LEDs: 12 High Brightness
Length of Cable (m): 2
Maximum Trigger Frequency (Hz): 30.00
Strobe Duration (µs): 30 - 300
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Diffuse Axial
Illumination Mode: Strobed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
