

63.5mm Clear Aperture, 30 Arcsec, Gold Retroreflector



Stock #46-190 3-5 DAYS

-

1

+

A\$1,560.00

ADD TO CART

Qty 1+
A\$1,560.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec):
30.00

Clear Aperture CA (mm):
63.5

Coating:
Protected Gold (700-2000nm)

Diameter (mm):
89.40

Exiting Wavefront Accuracy:
9.0λ

Substrate:  BOROFLOAT®
Surface Quality: 80-50
Mounting Threads: (6) ¼-20, (5) M6 x 1.0
Type: Retroreflector
Dimensional Tolerance (mm): ±1.6
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 700 - 2000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View