

635nm, 3mW Laser Diode Module, 120° Line Generator



Focusable Alignment Laser Diode Modules

Stock **#68-708** CLEARANCE 3-5 DAYS

- 1 +

A\$79.92

ADD TO CART

Qty 1+

A\$79.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Operating Current (mA):
Typical: 45
Maximum: 60

Operating Temperature (°C):
0 to +40

Operating Voltage (V):
Typical: 2.5
Maximum: 3.3

Outer Diameter (mm):
11.5

Output Power (mW): 3
Type: 120° Line Generator
Wavelength (nm): 635.00
Output Type: Free Space
Type of Laser: Diode
Color: Red
Fan Angle (°): 120.00
Length (mm): 30.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View