

656.3nm CWL, 0.50 FWHM, 25mm Dia. Ultra Narrow Filter



Stock #21-387 3-5 DAYS

1

A\$2,240.00

ADD TO CART

Qty 1-5
A\$2,240.00
Qty 6+
A\$2,008.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.25

Angle of Incidence (°):
0

Clear Aperture CA (mm):
21.00

Center Wavelength CWL (nm):

656.30
Full Width-Half Max FWHM (nm): 0.50
Substrate: ☐ Soda Lime Glass & Filter Glass
Minimum Transmission (%): >45
Type: Bandpass Filter
Note: Filter Design: Two-Cavity
Substrate Thickness (mm): 6 +0.00/-0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant