

676nm CWL, 11.8mm Dia. Bandpass Filter



Stock **#28-484** CLEARANCE 3-5 DAYS

-

1

+

A\$31.92

ADD TO CART

Qty 1+

A\$31.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
11.80

Optical Density OD (Average):
≥3.0

Center Wavelength CWL (nm):
676.00

Center Wavelength CWL Tolerance (nm):
±2

Full Width-Half Max FWHM (nm):
10.00

Minimum Transmission (%): 50
Surface Quality: 80-50
Thickness (mm): 4.60
Type: Bandpass Filter
Typical Applications: Kr Emission Line
Blocking Wavelength Range (nm): 200 - 1200
Dimensional Tolerance (mm): ±0.2

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View

