

TECHSPEC® 6mm Dia x 12mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens



Stock **#69-740** 3-5 DAYS

- 1 + **A\$127.20**

ADD TO CART

Qty 1-5
A\$127.20
Qty 6+
A\$101.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
12.00

Substrate: N-BK7

f/#:

Numerical Aperture NA: 0.25
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): 10.55
Center Thickness CT (mm): 2.20
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.43
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 6.20
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant