

TECHSPEC® 6mm Dia x 12mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#68-026** 3-5 DAYS

- 1 +

A\$95.20

ADD TO CART

Qty 1-5
A\$95.20
Qty 6+
A\$76.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
12.00

Substrate:
[N-BK7](#)

f/#:

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 10.55
Center Thickness CT (mm): 2.20
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.43
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 6.20
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View