

TECHSPEC® 6mm Dia. x 18mm FL VIS-EXT Coated, Double-Convex Lens



Stock **#89-132** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$67.20

ADD TO CART

Qty 1-9
A\$67.20
Qty 10+
A\$60.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.00 +0.000/-0.025

Back Focal Length BFL (mm):
17.26

Effective Focal Length EFL (mm):

18.00
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.20
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.7
Radius R₁=R₂ (mm): 18.22
Clear Aperture CA (mm): 5.4
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant