

TECHSPEC® 6mm Dia x 24mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens



Stock **#69-716** 3-5 DAYS

- 1 + **A\$127.20**

ADD TO CART

Qty 1-5
A\$127.20
Qty 6+
A\$101.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
24.00

Substrate:
[N-BK7](#)

f/#:

Numerical Aperture NA: 0.13
Coating: VS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 22.94
Center Thickness CT (mm): 1.60
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.23
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.40
Surface Quality: 60-40
Damage Threshold, Reference:  5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant