

TECHSPEC® 6mm Dia. x -12mm FL, VIS-NIR, Inked, Double-Concave Lens



Stock **#48-699-INK** [CONTACT US](#)

- 1 +

A\$81.60

ADD TO CART

Qty 1-9

A\$81.60

Qty 10+

A\$73.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
-12.00

Substrate: N-BK7
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Type: Double-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -12.33
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 5.4
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 1.59
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -12.57
Surface Quality: 40-20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View