

6mm FL Compact Fixed Focal Length Lens



Fixed Focal Length Lenses

Stock **#68-674** 3-5 DAYS

[Similar Products](#)



1



A\$680.00

ADD TO CART

Qty 1+

A\$680.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
174.00

Iris Option:
Variable

Length (mm):
34.00

Horizontal Field of View, 1/2" Sensor:
57.3°

Filter Thread:

M25.5 x0.50
Maximum Diameter (mm): 31.0
Weight (g): 60.00
Maximum Rear Protrusion (mm): 8.1
Maximum Image Circle (mm): 8.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 6.00
Maximum Sensor Format: 1/2"
Working Distance (mm): 200 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View