

TECHSPEC® 6" Dia, 24" FL Uncoated, Spherical Mirror



Stock **#43-968** 3-5 DAYS

- 1 + **A\$772.80**

ADD TO CART

Qty 1-4
A\$772.80
Qty 5+
A\$656.00
Volume Pricing
Request Quote

Get Product Downloads



Substrate: □
BOROFLOAT® SUPREMAX®

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:

N4
Diameter (inches): 6.0
Diameter (mm): 152.40 +1.5/-0
Diameter Tolerance (inches): +0.06/-0
Effective Focal Length EFL (inches): 24.00
Effective Focal Length EFL (mm): 609.60
Radius of Curvature (mm): 1,219.20
Aperture (f/#): f/4
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 1.00
Edge Thickness ET (mm): 25.40
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View