


700nm, 12.5mm Dia., OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock **#15-250** 3-5 DAYS

- 1 + **A\$131.20**

ADD TO CART

Qty 1-9
A\$131.20
Qty 10+
A\$118.08
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm): 700.00 ±14
Substrate:  BOROFLOAT®
Coating: Hard Coated
Rejection Wavelength (nm): 730 - 900
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 400 - 675
Type: Shortpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A Section 3.4.1
Wavelength Range (nm): 400 - 900

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View