

TECHSPEC® 70mm, 120mm Radius, English Goniometer



TECHSPEC® Goniometers



Stock #66-532

CONTACT US



1



A\$1,102.40

ADD TO CART

Qty 1-2

A\$1,102.40

Qty 3+

A\$960.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:

English
Stage Size (mm): 70 x 70
Travel (°): ±10
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 6
Mounting Threads: (9) ¼-20, (4) 6-32, (8) 2-56
Radius R (mm): 120
Resolution (arcmin): 5
Stage Size (inches): 2.75 x 2.75
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant