

70mm Color Corrected Schneider Compact VIS-NIR Lens



Schneider Compact VIS-NIR Lenses

Stock **#59-820** [CONTACT US](#)

-

1

+

A\$3,766⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$3,766.00 each
Need More?	Request Quote

Product Downloads

General	
Schneider Compact VIS-NIR Lenses	Series:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
74.00	Length (mm):

31.5	Maximum Diameter (mm):
42	Outer Diameter (mm):
200	Weight (g):
Optical Properties	
9.0°	Horizontal Field of View, 2/3" Sensor:
11.00	Maximum Image Circle (mm):
70.00	Focal Length FL (mm):
734 - ∞	Working Distance (mm):
f/2.2 - f/11	Aperture (f/#):
<0.1	Distortion (%):
VIS-NIR Color Corrected	Lens Wavelength Range:
Sensor	
2/3"	Maximum Sensor Format:
3.45	Pixel Size (µm):
Threading & Mounting	
M40.5 x 0.50	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details


- Up to 4/3", C-Mount Lens
- Spectral Range of 400-1000nm with Color Corrected Options
- 4.8mm to 50mm Focal Length


Schneider's Standard VIS-NIR lenses can accommodate up to a 4/3" sensor (22mm image circle) but will need to be refocused when switching between VIS and NIR wavelengths.

This series of lenses features a robust mechanical design, lockable focus, lockable iris, and filter mount threads, making them ideal for typical industrial settings. The optical design is an excellent match for high pixel depth cameras. Their excellent optical performance over the entire working distance range corresponds perfectly to the capabilities of high resolution sensors.


Note: Lenses with M62 x 0.75 filter thread require [#59-825](#) filter thread adapter.

Technical Information





Typical
Transmission



Stock No.	A	B	C	D
#59-819	41.0mm	6.3mm	2.8mm	37.3mm
#64-764	40.9mm	3.75mm	2.5mm	31.5mm
#56-533	32.4mm	5.1mm	0.9mm	31.5mm
#56-534	42.7mm	5.8mm	1.2mm	31.5mm
#56-535	33.4mm	4.3mm	12.4mm	31.5mm
#56-536	36.9mm	3.8mm	8.2mm	31.5mm
#56-537	34.7mm	3.8mm	2.6mm	31.5mm
#59-820	74.0mm	3.8mm	4.3mm	42mm

Stock No.	A	B	C	D
#59-821	46.1mm	4.1mm	0.3mm	37.3mm
#59-822	40.9mm	3.8mm	2.5mm	31.5mm
#59-823	34.7mm	3.8mm	2.6mm	31.5mm
#59-824	36.9mm	3.8mm	8.2mm	31.5mm

