


TECHSPEC® 70mm, English Micrometer Tilt Stage



70mm Micrometer Tilt Stage

Stock #66-549 4 In Stock

-

1

+

A\$824⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	A\$824.00 each
Qty 3+	A\$719.20 each
Need More?	Request Quote

Product Downloads

General

Type:

English

Physical & Mechanical Properties

Type of Movement:

Tip-Tilt

Stage Size (mm):

70 x 70

Travel (°):

±3	
	Construction:
Aluminium Stage	
	Load Capacity (kg):
3	
	Resolution (arcsec):
53	
	Stage Size (inches):
2.76 x 2.76	
	Weight (kg):
0.35	

Hardware & Interface Connectivity

	Type of Drive:
Metric Micrometer	

Threading & Mounting

	Mounting Threads:
(7) ¼-20, (4) 6-32, (8) 2-56	

Regulatory Compliance

	RoHS 2015:
Exempt	
	Certificate of Conformance:
View	
	REACH 241:
Contains SVHC(s)	

Product Details

- Metric and English Hole Pattern Versions Available
 - Tilt Control in Two Axes (Kinematic Movement)
 - Precision Micrometer Drive
 - Mechanically Compatible to Other TECHSPEC® Stages
- TECHSPEC® Tip-Tilt Stages are available in three different stage sizes from 30mm square to 70mm square. Each size is offered in Metric or English hole pattern versions and features precision micrometer movement for movement repeatability. Each stage is designed to integrate with TECHSPEC® components, further enhancing flexibility and allowing the user to create any number of axes in different configurations. TECHSPEC Tip-Tilt Stages are ideal for tilt control of both optics and mounting posts. [Bottom adapter plate](#), sold separately, is required to mount 30mm and 40mm stages to a standard breadboard.

Technical Information

