

TECHSPEC® 70mm, Side Drive, Standard Top, Metric Micrometer Stage



70mm, Side Drive, Solid Top, Micrometer Stage

Stock **#66-436** 3-5 DAYS

- 1 + **A\$696.00**

ADD TO CART

Qty 1-2

A\$696.00

Qty 3+

A\$607.36

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:

Linear (X)

Guide System:

Crossed Roller Bearing

Type of Drive:

Metric Micrometer

Drive Orientation:

Side Drive
Type: Metric
Stage Size (mm): 70 x 70
Travel (mm): 13
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 8
Mounting Threads: (8) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 2.75 x 2.75
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)