

TECHSPEC® 75 Dia., 1.1mm Thick, MgF2 Coated, Gorilla Glass® Window



Gorilla® Glass Windows



Stock #22-856 [CONTACT US](#)

-

1

+

A\$148.00

ADD TO CART

Qty 1-5

A\$148.00

Qty 6+

A\$114.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):
8

Clear Aperture (%) : 90.00
Clear Aperture CA (mm) : 67.50
Diameter (mm) : 75.00 ±0.13
Thickness (mm) : 1.10 (nominal)
Coating : MgF ₂ (400-700nm)
Coating Specification : R _{avg} ≤1.75% @400 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 7.58 (0 to +300°C)
Density (g/cm³) : 2.39
Edges : Fine Ground
Index of Refraction n_d : 1.5
Poisson's Ratio : 0.22
Substrate : Gorilla® Glass
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 400 - 700
Young's Modulus (GPa) : 70

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant