

TECHSPEC[®] 75 x 75mm 70R/30T, VIS Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock #48-908 3-5 DAYS

-

1

+

A\$515.20

ADD TO CART

Qty 1-5

A\$515.20

Qty 6+

A\$412.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: 70/30 ±5% @ 550nm, ±10% @ 400 - 700nm

Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @400 - 700nm
Construction: Plate
Dimensions (mm): 75.0 x 75.0 +0.0/-0.25
Edges: Cut with 0.25mm maximum edge chip
Note: Beamsplitter-coated side is marked with a black dot
Parallelism (arcmin): ≤ 3
Reflection/Transmission Ratio (R/T): 70/30
Substrate:  N-BK7
Surface Flatness (P-V): 1λ per inch
Surface Quality: 60-40
Thickness (mm): 3.00 ±0.25
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant