

TECHSPEC® 76.2 x 646mm EFL 15° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock **#35-597** 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$1,176.00**

ADD TO CART

Qty 1-5
A\$1,176.00
Qty 6+
A\$1,058.40
Volume Pricing
Request Quote

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
76.20 +0.00/-0.38

Effective Focal Length EFL (mm):
646.00

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 1,270.00
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm
Off-Set Angle (°): 15
Parent Focal Length PFL (mm): 635.00
Surface Figure, RMS: 3/4λ
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 400 - 2000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #63-375
Substrate: Aluminum 6061-T6
Y Offset (mm): 167.2
Reflected Wavefront, RMS: 3/2λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant