

76.2 x 76.2mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#69-252** CLEARANCE 3-5 DAYS



1



A\$60.80

ADD TO CART

Qty 1-5

A\$60.80

Qty 6+

A\$48.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):

4 - 6λ

Substrate:

Float Glass

Surface Quality:

80-50

Dimensions (mm):

76.2 x 76.2 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 76.20
Width (mm): 76.20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant