

76.2mm Clear Aperture 8R/92T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock #39-486 3-5 DAYS

⊖ 1 ⊕ **A\$384.00**

ADD TO CART

Qty 1-10

A\$384.00

Qty 11+

A\$326.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
76.2

Coating:
Uncoated

Construction:
Pellicle

Diameter (mm):
88.90

Housing:
Black Anodized Aluminum

Index of Refraction n_d :
1.5

Mount Thickness (mm):
6.35

Reflection/Transmission Ratio (R/T):
8/92 \pm 5%

Substrate:
Nitrocellulose

Surface Quality:
40-20

Type:
Pellicle Beamsplitter

Wavelength Range (nm):
400 - 2200

Mounting Threads:
2-56

Thickness (μ m):
2 +0.3/-0.2

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)
