

6.5mm Diameter x 6mm FL, PCX Condenser Lens



Stock **#43-480** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$38.40

ADD TO CART

Qty 1-10
A\$38.40
Qty 11+
A\$33.60
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.50

Effective Focal Length EFL (mm):
6.00

Numerical Aperture NA:
0.58

Substrate:

Float Glass
Focal Length Tolerance (%): ±7
Coating: Uncoated
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 3.40 ±0.2
f/#: 0.86
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View