

80µm Aperture Diameter, Mounted, Precision Pinhole



80µm Aperture Diameter, Mounted, Precision Pinhole, #84-067

Stock **#84-067** 3-5 DAYS



1



A\$120.00

ADD TO CART

Qty 1-5

A\$120.00

Qty 6+

A\$105.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Mounted

Outer Diameter (mm):
25 +0.4/-0.000

Construction:
Stainless Steel

Fixed Aperture Diameter (µm):

80
Thickness (mm): 0.03 Nominal
Aperture Tolerance (µm): ±5
Mount Thickness (mm): 1.25 ±0.05
Aperture Centration (µm): ±125

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

