

# 830 Grooves, 12.7mm Sq, 29.9° Groove Angle Grating



Stock #49-577 3-5 DAYS

- 1 + **A\$160.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$160.00                     |
| Qty 10+                       |
| A\$144.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Groove Density (grooves/mm):  
830

Wavelength Range (nm):  
400 - 700

Blaze Angle (°):  
29.9

|                                                                    |
|--------------------------------------------------------------------|
| <b>Dimensions (mm):</b><br>12.70 x 12.70                           |
| <b>Construction:</b><br>Blazed (Ruled) Grating                     |
| <b>Length (mm):</b><br>12.70                                       |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">B270</a> |
| <b>Thickness (mm):</b><br>3.00 ±0.5                                |
| <b>Type:</b><br>Transmission Diffraction Grating                   |
| <b>Wavelength:</b><br>VIS                                          |
| <b>Width (mm):</b><br>12.70                                        |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.5                   |
| <b>Groove Angle (°):</b><br>29.9                                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---