

[See all 20 Products in Family](#)

830 Grooves, 25mm Square, 1250nm NIR Ruled Grating



Stock **#46-080** **20+ In Stock**

⊖ 1 ⊕ **A\$296^{.00}**

ADD TO CART

Volume Pricing	
Qty 1-9	A\$296.00 each
Qty 10-24	A\$266.40 each
Need More?	Request Quote

Product Downloads

General

Reflective Diffraction Grating **Type:**

Physical & Mechanical Properties

25.0 x 25.0 ±0.5 **Dimensions (mm):**

90 **Clear Aperture (%):**

Ruled Grating **Construction:**

Direction of Grooves:	
Parallel to Short Dimension	
Length (mm):	
25.00	
Thickness (mm):	
9.50 ±0.5	
Width (mm):	
25.00	
Alignment of Grooves to Edge (°):	
±0.5	

Optical Properties

Groove Density (grooves/mm):	
830	
Wavelength Range (nm):	
700 - 3000	
Blaze Wavelength (nm):	
1200	
Blaze Angle (°):	
29.87	
Coating:	
Bare Gold	
Substrate: <input type="checkbox"/>	
Float Glass	

Regulatory Compliance



RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	

Product Details

- Increased Reflection from 700 - 1100nm
- Near-IR (NIR) Reflective Gold Gratings are ruled gold-coated versions of our commercial gratings. These gratings provide increased reflection from 700 - 1100nm. This makes them an excellent choice for applications such as fiber optic pulse compression and spectroscopy setups using [silicon detectors](#). Near-IR (NIR) Reflective Gold Gratings feature a float glass substrate and a ruled grating construction. The gratings are available in three sizes, with varying groove densities and blaze wavelengths.

Handling Gratings: Gratings require special handling, making them prone to fingerprints and aerosols. Gratings should only be handled by the edges. Before attempting to clean a grating, please [contact us](#).

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

;