

[See all 55 Products in Family](#)

## 830nm 5mW Pigtailed Laser Diode



Stock **#23-788** **2 In Stock**

- 1 + AS\$1,424.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	AS\$1,424.00 each
Qty 10+	AS\$1,281.60 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads



### General

Diode **Type of Laser:**  
IIIb **Laser Class - CDRH:**

### Physical & Mechanical Properties

1 **Length of Fiber (m):**

## Optical Properties

0.12 Numerical Aperture NA:

Fiber-Coupled Spatial Mode:

5 Fiber Diameter (µm):

830.00 ±15 Wavelength (nm):

NIR Color:

## Electrical

5 Output Power (mW):

## Hardware & Interface Connectivity

5.0 Operating Voltage (V):

Power Supply:  
Power Supply Required and Sold Separately.  
USA: [#73-818](#)  
Europe: [#73-818](#)  
Japan: [#13-640](#)  
Korea: [#33-770](#)  
China: [#73-818](#)

FC/PC Connector:

## Environmental & Durability Factors

+15 to +30 Operating Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 233:

## Product Details

- Single Mode Fiber with FC/PC Connector
- 1 to 100mW Output Power and 405 to 1550nm Wavelength Options
- Integrated Driver for Easy Operation

Pigttailed Laser Diode Modules feature an integrated 1m long, single mode fiber with an FC/PC connector. These laser diodes also feature an integrated driver for plug and play operation, only requiring a 5V external power supply ([#73-818](#)). Pigttailed Laser Diode Modules are available with VIS and NIR wavelengths ranging from 405 to 1550nm, with output powers ranging from 1 to 100mW. Their plug and play operation make these laser diodes ideal for a wide range of laboratory and OEM applications.