

85 x 50mm English Base Plate



Stock **#58-998** 20+ In Stock

-

1

+

A\$55^{.20}

ADD TO CART

Volume Pricing	
Qty 1+	A\$55.20 each
Need More?	Request Quote

Product Downloads

General

Type:

English

Physical & Mechanical Properties

Length (mm):

85.00

Width (mm):

50.00

Thickness (mm):

7.00

Construction:

Black Anodized Aluminum	
Number of Slots:	
6	
Threading & Mounting	
Mounting Threads:	
(4) 8-32, (5) 1/4-20	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 250:	
Compliant	

Product Details

- Two Size Options
- Two Platform Options: English or Metric
- English: Four #8-32 holes on 1/2" Square and Four 1/4-20 Holes on 1" Square
- Metric: Four M4 x0.7 holes on 12.5mm Square and Four M6 x 1 Holes on 25mm Square
- Anodized Aluminum Construction

Base Plates have Metric or English threaded holes and additional center trapped hole (M6 x 1 or 1/4-20). Base Plates also have extended center slots that ensure full use on matching metric or English breadboard patterns. 85mm x 50mm Base Plates have same tapped holes and slots as 60mm x 35mm Base Plates, but with extra short slots for added flexibility.

Technical Information

