

850nm, 12.5mm Dia., OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock #15-219 3-5 DAYS



1



A\$131.20

ADD TO CART

Qty 1-9

A\$131.20

Qty 10+

A\$118.08

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 850.00 ±17
Substrate:  BOROFLOAT®
Coating: Hard Coated
Rejection Wavelength (nm): 600 - 810
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 890 - 1600
Type: Longpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A Section 3.4.1
Wavelength Range (nm): 600 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View