

50mm Max. Aperture, Mounted Iris Diaphragm



86mm Outer Diameter, Mounted Iris Diaphragm, #53-917

Stock **#53-917** 3-5 DAYS

- 1 +

A\$244.80

ADD TO CART

Qty 1-4
A\$244.80
Qty 5+
A\$215.84
Volume Pricing
Request Quote

Get Product Downloads

Type: Mounted
Minimum Aperture (mm): 2.50
Maximum Aperture (mm): 50.0
Outer Diameter (mm):

86.0
Construction: Blackened Brass Housing, Stainless Steel Leaves, Stainless Steel Pin Actuators, Black Anodized Aluminum Mount
Inner Diameter (mm): 70.00
Lever Diameter (mm): 3.00
Lever Length (mm): 15.00
Mounting Threads: 1/4-20
Set Screw Thread: 6-32
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)