

# 86mm Travel, Long Travel Single Axis Movement Stage



#53-384

Stock #53-384 3-5 DAYS



1



A\$617.60

ADD TO CART

Qty 1-9

A\$617.60

Qty 10+

A\$544.96

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:

Linear (X)

Guide System:

Dovetail

Type of Drive:

Rack and Pinion

Type:

|                                                               |
|---------------------------------------------------------------|
| English                                                       |
| <b>Stage Size (mm):</b><br>25 x 200                           |
| <b>Travel (mm):</b><br>86 (±43)                               |
| <b>Load Capacity (kg):</b><br>3.5 Horizontal, 2.1 Vertical    |
| <b>Mounting Threads:</b><br>Stage: (2) ¼-20<br>Base: (4) 8-32 |
| <b>Note:</b><br>Not Lockable                                  |
| <b>Straight Line Accuracy (µm):</b><br>60                     |
| <b>Travel Per Knob Rotation (mm):</b><br>15                   |
| <b>Weight (g):</b><br>800                                     |
| <b>Table Size (mm):</b><br>25 x 105                           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Reach 224:</b><br><a href="#">Contains SVHC(s)</a>      |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |