

[See all 63 Products in Family](#)

Type-A to Micro-B, USB 3.0 Cable, 8m



Certified USB3.0, Standard-A to Micro-B Cable



Stock **#25-631** **2 In Stock**

⊖ 1 ⊕ **A\$337⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	A\$337.60 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory **Type:**

Hardware & Interface Connectivity

8 **Length of Cable (m):**

USB 3.0, Standard-A to Micro-B **Connector:**

Certificate of Conformance:

[View](#)

Product Details

- Resolutions Up to 20MP
- Sensor Sizes from 1/2.5" to 1.1"
- Right Angle Housing and Board Level Configurations Available

Pixelink® USB 3.0 Cameras are high resolution and high-speed solutions to applications ranging from biometrics to surveillance. Pixelink® USB 3.0 Cameras feature resolutions of up to 20MP, frame rates of up to 170fps, and USB 3.0 compatibility for power and high data throughput. The right angle housing configurations also feature a GPIO to enable triggering to ease system integration. Pixelink® USB 3.0 Cameras also compatible with sensor sizes ranging from 1/2.5" to 1.1" and are ideal for inspecting weld and PCB and flat panel displays. These cameras are available in monochrome or color.

Note: Mounting Adapters are only designed for enclosed camera models, and not board-level. If your camera ends in "-BL", it does not have a compatible mount.

Pixelink Capture is a free, user-friendly application included with all Pixelink cameras, offering real-time image and video capture through an intuitive graphical interface. In contrast, the Pixelink SDK is a comprehensive development toolkit for Windows and Linux that enables developers to build custom applications with full camera control via C/C++, .NET, or Python. The SDK is available as a trial download, allowing users to evaluate its capabilities before purchasing a license. Links to software downloads (SDK and Capture) are available on the product pages.
