

TECHSPEC® 8mm Max Aperture Motorizable Iris



High Performance Motorizable Iris



Stock **#34-287** 3-5 DAYS

1

A\$112.00

ADD TO CART

Qty 1-4
A\$112.00
Qty 5+
A\$98.72
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.9

Maximum Aperture (mm):

8.0
Outer Diameter (mm): 14.8
Construction: Brass-Spring Steel
Number of Leaves: 8
Thickness (mm): 6.00
Pitch Diameter (mm): 12.55

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)