

90° 355nm Crystalline Quartz Polarization Rotator



Crystalline Quartz Polarization Rotators

Stock **#34-310** CLEARANCE 3-5 DAYS

-

1

+

A\$487.92

ADD TO CART

Qty 1+

A\$487.92

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
>18.0

Coating:
R_{avg} <0.2% per surface

Design Wavelength DWL (nm):
355

Diameter (mm):
25.40

Substrate: ☐

Crystalline Quartz
Length (mm): 25.40
Surface Quality: 20-10
Type: Polarization Rotator
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 @ 633nm
Parallelism (arcsec): <10
Mount Thickness (mm): 6.0
Damage Threshold, By Design: ☐ >10 J/cm² @ 10ns
Width (mm): 6.00
Polarization Rotation: 90° (clockwise)
Rotational Accuracy: <5 arcmin
Mount: Black Anodized Aluminum

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View