

950nm CWL, 50nm FWHM, 50mm Mounted Diameter



Stock **#87-196** 3-5 DAYS

[Additional Bandwidths](#)

1

A\$761.60

ADD TO CART

Qty 1-9
A\$761.60
Qty 10+
A\$685.12
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Clear Aperture CA (mm): 42.0
Center Wavelength CWL (nm): 950.00 ±15
Center Wavelength CWL Tolerance (nm): ±15
Full Width-Half Max FWHM (nm): 50.00 ±15
Full Width-Half Max FWHM Tolerance (nm): ±15
Minimum Transmission (%): ≥55
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: InGaAs
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View