

9mm Dia. x 36mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-072** CLEARANCE 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$31.92

ADD TO CART

Qty 1+

A\$31.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
9.00 +0.00/-0.10

Effective Focal Length EFL (mm):
36.00

Back Focal Length BFL (mm):
34.89

Coating:
Uncoated

Substrate: [N-BK7](#)

Focal Length Tolerance (%): ±1
Centering (arcmin): 6.00
Center Thickness CT (mm): 1.70
Edge Thickness ET (mm): 1.15
Radius R₁ (mm): 18.61
Clear Aperture CA (mm): ≥7.65
f#: 4.00
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View