

[See all 3 Products in Family](#)

Achromatic Lens 6.25mm Dia. x 35mm FL, Uncoated



Stock **#32-306** CLEARANCE **7 In Stock**

- 1 + **A\$21^{.60}**

ADD TO CART

Volume Pricing	
Qty 1+	A\$21.60 each
Need More?	Request Quote

Product Downloads

#Max Edge Thickness of Curved Optic (mm):
3.8600000000

#Min Edge Thickness of Curved Optic (mm):
2.3600000000

General	
Achromatic Lens	Type:
Physical & Mechanical Properties	
2.30	Center Thickness CT 1 (mm):
	Center Thickness CT 2 (mm):

0.90	
	Diameter (mm):
6.2500000000 +0.00/-0.05	
	Edge Thickness ET (mm):
2.86	
	Center Thickness Tolerance (mm):
±0.1	
	Centering (arcmin):
1.00	
Optical Properties	
	Back Focal Length BFL (mm):
33.59	
	Coating:
Uncoated	
	Effective Focal Length EFL (mm):
35.0000000000	
	Substrate:
N-BK7 / N-SF5	
	Numerical Aperture NA:
0.08	
	Radius R ₁ (mm):
23.1400000000	
	Radius R ₂ (mm):
-14.51	
	Radius R ₃ (mm):
-38.86	
	Surface Quality:
40-20	
	Focal Length Tolerance (%):
±2	
	Focal Length Specification Wavelength (nm):
632.8	
	f/#:
5.6	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- Discounts up to 80% Off
- Quantities Extremely Limited
- Final Sale, No Returns

Shop the EO Mega Clearance presentations for the hottest deals on component-level products. Quickly browse the best optics, [imaging](#), and [photonics](#) deals you will ever see. Quantities are extremely limited and are sold on a first-come-first-serve basis.

Hurry, while supplies last. EO Mega Clearance products will never be sold again. Check out our standard [clearance products](#) for even more deals!

All products are final sale; EO will not accept returns. No additional information is available other than what is listed.

Compatible Mounts